

# Lovibond® Water Testing Tintometer® Group



## Платиново-кобальтовая шкала EC 2000

Colour measurement of water



- Immediate & Accurate
- Straight from the Box
- Guaranteed Agreement with International Standards
- Display Results with On-Screen Colour and Numerical Options

Номер заказа: 162010

### Dual Ability to View Colour Comparison

- On-screen colour
- On-screen numerical display

### Easy Transition from Visual to Electronic Measurements

Some colour graders who are used to the traditional comparator series sometimes find the upgrade to an electronic system daunting. The assurance of relying on physical colour difference is diminished. This transition has now been made easy.

### Touch Screen Technology

Enables you to easily programme the instruments with instinctive menus on screen.

### Programmable Settings

You can set language\*, date and time, view preferences and create projects with individual tolerance settings.

### On-Screen Warning System

You can react immediately to results that might be out of tolerance with immediate information on the sample.

- Within tolerance = green
- Outside tolerance = red
- On border of tolerance = amber

### User Friendly Ergonomics and Intuitive Interface

You are guaranteed to be up and running quickly and easily supported.

### Easy storage and sharing of results

Large data storage (> 20,000 readings) and USB connectivity ensure your results can be stored and easily shared.

### Single Scale Measurement

The EC 2000 Pt Co provides you an individual scale to measure Platinum Cobalt/Hazen/Apha Colour (ASTM D 1209).

\* Supported languages: English, French, German, Spanish, Italian, Chinese, Japanese, Russian.

## Промышленность

Нефтяная промышленность | Пищевая промышленность и производство напитков | Фармацевтическая промышленность | Химическая промышленность

## Применение

Минеральные масла и воски | Пищевые масла и жиры | Фармацевтическая и косметическая продукция | Химикаты

## Платиново-кобальтовая шкала EC 2000

Advance from visual (subjective) to electronic (objective) colour measurement.

High precision with 50 mm cuvette path length!

## Технические данные

<b>Colour Type</b>	Transparent
<b>Дисплей</b>	Size: 3.5 inch; Resolution: 320 x 240; Colour: 24 Bit (True Colour)
<b>Интерфейсы</b>	USB
<b>Встроенная память</b>	> 20000 измерений
<b>Электроснабжение</b>	USB 2.0 (разъем mini USB) 4 батареи (AA)
<b>Клавиатура</b>	Мембранная клавиатура с 3 клавишами
<b>Корпус</b>	Огнезащитное средство ABS
<b>Переносимость</b>	Портативный
<b>Сенсорный экран</b>	Нет
<b>Языки интерфейса пользователя</b>	Немецкий, Английский, Французский, Испанский, Итальянский, Русский, Китайский, Японский
<b>Размеры</b>	106 x 57 x 210 mm

## Объем поставки

- Instrument in carrying case
- Power Supply (UK, EU, US Plug)
- USB Cable
- 4 AA Batteries
- Liquid Reference Standard 1
- Liquid Reference Standard 2
- Glass cuvette
- Glass standard
- CD with Software (Windows®)
- Instruction Manual

Заголовок	Номер заказа
Жидкостный эталон для платиново-кобальтовой шкалы 0 - 500 мл	133991
Жидкостный эталон для платиново-кобальтовой шкалы 15 - 500 мл	134160
Жидкостный эталон для платиново-кобальтовой шкалы 30 - 500 мл	134170
Жидкостный эталон для платиново-кобальтовой шкалы 15 - 60 мл	135049
Жидкостный эталон для платиново-кобальтовой шкалы 0 - 60 мл	135059
Устройство для питания от сети с портом USB для EC 2000	190620
Кабель USB 2,0 A - разъем Micro B	190630
Одноразовые пластиковые кюветы 50 мм	352101

### Tintometer GmbH

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
Германия

### The Tintometer Limited

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
sales@lovibond.uk  
www.lovibond.com  
ВЕЛИКОБРИТАНИЯ

### Tintometer China

Room 1001, China Life Tower  
16 Chaoyangmenwai Avenue,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 App. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
Китай

### Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,  
Lebu Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Малайзия

### Tintometer Brazil

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
Бразилия

### Tintometer Inc.

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
США

### Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
Индия

### Tintometer Spain

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
Испания

Возможны технические изменения

Отпечатано в Германии

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies