

# Lovibond® Water Testing Tintometer® Group



## EC 2000 铂钴

Colour measurement of water



- Immediate & Accurate
- Straight from the Box
- Guaranteed Agreement with International Standards
- Display Results with On-Screen Colour and Numerical Options

货号: 162010

### Dual Ability to View Colour Comparison

- On-screen colour
- On-screen numerical display

### Easy Transition from Visual to Electronic Measurements

Some colour graders who are used to the traditional comparator series sometimes find the upgrade to an electronic system daunting. The assurance of relying on physical colour difference is diminished. This transition has now been made easy.

### Touch Screen Technology

Enables you to easily programme the instruments with instinctive menus on screen.

### Programmable Settings

You can set language\*, date and time, view preferences and create projects with individual tolerance settings.

### On-Screen Warning System

You can react immediately to results that might be out of tolerance with immediate information on the sample.

- Within tolerance = green
- Outside tolerance = red
- On border of tolerance = amber

### User Friendly Ergonomics and Intuitive Interface

You are guaranteed to be up and running quickly and easily supported.

### Easy storage and sharing of results

Large data storage (> 20,000 readings) and USB connectivity ensure your results can be stored and easily shared.

### Single Scale Measurement

The EC 2000 Pt Co provides you an individual scale to measure Platinum Cobalt/Hazen/Apha Colour (ASTM D 1209).

\* Supported languages: English, French, German, Spanish, Italian, Chinese, Japanese, Russian.

## 行业

化工行业 | 医药行业 | 油气 | 食品和饮料行业

## 应用

化工产品 | 石油和石蜡 | 药品和化妆品 | 食用油和脂肪

## EC 2000 铂钴

Advance from visual (subjective) to electronic (objective) colour measurement.

High precision with 50 mm cuvette path length!

## Technical Data

颜色类型	Transparent
显示	Size: 3.5 inch; Resolution: 320 x 240; Colour: 24 Bit (True Colour)
数据接口	USB
内置存储器	> 20000 次测量
电源	USB 2.0 (mini USB 插头) 4个电池 (AA)
按键	3 按键薄膜键盘
外壳	ABS 防火剂
便携性	手提
触摸屏	no
多语言操作界面	德文, 英文, 法文, 西班牙, 意大利, 俄语, 中文, 日语
尺寸	106 x 57 x 210 mm

## 标准配置文本

- Instrument in carrying case
- Power Supply (UK, EU, US Plug)
- USB Cable
- 4 AA Batteries
- Liquid Reference Standard 1
- Liquid Reference Standard 2
- Glass cuvette
- Glass standard
- CD with Software (Windows®)
- Instruction Manual

标题	货号
液体标准铂钴色标 0 - 60 ml	133991
液体标准铂钴色标 15 - 60 ml	134160
液体标准铂钴色标 30 - 500 ml	134170
液体标准铂钴色标 15 - 500 ml	135049
液体标准铂钴色标 0 - 500 ml	135059
其他	190620
其他	190630
50 mm 一次性塑料比色杯	352101

### Tintometer GmbH

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
德国

### The Tintometer Limited

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
sales@lovibond.uk  
www.lovibond.com  
英国

### Tintometer China

9F, SOHO II C.  
No.9 Guanghualu,  
Chaoyang District,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 Ext. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
中国

### Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
马来西亚

### Tintometer Brazil

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
巴西

### Tintometer Inc.

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
美国

### Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
印度

### Tintometer Spain

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
西班牙