

Lovibond® Water Testing Tintometer® Group



SD 335 Multi (基础设备)



- Intuitive user interface with graphical LCD-display
- Galvanically isolated measuring inputs
- Data transfer via Micro-USB in CSV format
- Robust protective armoring with two electrode holders

货号: 724830

Modern technology

Due to galvanic isolation the temperature and two other parameters can be determined and displayed simultaneously.

Intuitive Handling

The combination of user-friendly operation and graphic LCD display in 7 different languages makes the portable measuring instrument the ideal companion for daily use in water analysis.

Data management

Measurement data including time stamp and location ID can be recorded with the data logger function. Via the micro-USB interface, the data can be easily transferred to a computer and processed without the need of additional software.

Protective armoring

The protective armoring with two electrode holders guarantees safe working even in extreme environmental conditions at all times. The stand attached to the back of the housing can be used conveniently as a hanger or belt clip.

Additional features

The range of functions is completed by the status display for the rechargeable NiMH batteries, the self-diagnosis of the sensors and much more.

行业

NGO | 其他行业 | 化工行业 | 医药行业 | 市政 | 油气 | 海洋工业 | 能源 | 食品和饮料行业

SD 335 Multi (基础设备)

Waterproof multiparameter handheld instrument for the simultaneous determination of temperature and two other parameters: pH, ORP, conductivity/TDS/salinity and dissolved oxygen (O₂-concentration/O₂-saturation)

Technical Data

显示	带图形显示的背光LCD
数据存储	手动记录仪, 按键式。自动记录仪, 循环式, 时间间隔可调。
Auto – OFF	是
电源	3 NiMH-battery pack (AAA) Micro-USB
便携性	手提
温度补偿	是
保护等级	IP 67
一致性	CE RoHS WEEE
尺寸	100 x 164 x 37 mm

标准配置文本

- 带有电极支架 (2个) 的防护装甲仪器
- 镍氢电池组
- 微型USB电缆
- 使用说明书
- 保固资讯
- 案件

标题	货号
pH-缓冲溶液 10.01 (25 °C) 蓝, 90 ml 可回溯至 N.I.S.T.	721249
pH-缓冲溶液套件 pH 4, pH 7, pH 10 (25 °C), 90 ml	721250
pH 缓冲溶液 4.01 (25 °C) 红, 1 升, 可回溯至 N.I.S.T.	721252
pH-缓冲溶液 7.00 (25 °C) 黄, 1 升, 可回溯至 N.I.S.T.	721254
pH-缓冲溶液 10.01 (25 °C) 蓝, 1 升, 可回溯至 N.I.S.T.	721256
校准溶液 1413 µS/cm, 500ml, 可回溯至 N.I.S.T.	722250
氧电极 SD 300 / SD 315 Oxi 服务套件由 3 个替换薄膜头和 100 ml KOH (1.18 mol/l) 电解质溶液组成	724670
SD 335 Multi 系列的带泡沫箱子	725080
用于 pH / ORP 的 3 M KCl 存储溶液, 25 毫升	726402
用于 pH / ORP 的 3 M KCl 存储溶液, 100 毫升	726404
电导率溶液 (1413 µS/cm)--90 毫升--可回溯至 N.I.S.T.	726654
电导率溶液 (12.88 mS/cm)--90 毫升--可回溯至 N.I.S.T.	726684

标题	货号
Redox 校准溶液, 470 mV, 100 ml	195070
KOH 100, 替代电解质, 100 毫升, 用于 SD 310 / SD 315 Oxi	19801130
用于 SD 320 / SD 325 Con 的 LC 12, 最高 200 mS/cm	19805040
用于 SD 320 / SD 325 Con 的 LC 16, 最高 1000 mS/cm	19805045
用于 SD 310 / SD 315 Oxi 的氧电极, 带 2 m 电缆, 铂阴极/铅阳极	19805050
用于 SD 310 / SD 315 Oxi 的氧电极, 带 10 m 电缆, 铂阴极/铅阳极	19805051
用于 SD 310 / SD 315 Oxi 的氧电极, 带 30 m 电缆, 铂阴极/铅阳极	19805052
氧电极 SD 310 / SD 315 Oxi 的保护帽用于深度测量 (PVC)	19805055
氧电极 SD 310 / SD 315 Oxi 的保护帽用于深度测量 (黄铜)	19805056
存储/校准瓶	19805057
pH 电极, 塑料/凝胶, 226 型, 无温度传感器, BNC 连接器	721226
pH 电极, 塑料/凝胶, 231 型, 温度传感器 NTC30k 欧姆, BNC 连接器 4 mm 用于 SD 300 / SD 305 pH (套件 1)	721231
带玻璃轴/凝胶的 pH 电极, 235 型, 无温度传感器, 用于 SD 300 / SD 305 pH 的 BNC 连接器	721235BNC
Redox 电极, 塑料/凝胶, BNC 连接器, 约 1 m 电缆	721242
Pt1000, 温度传感器, 金属, 直径 3 mm (套件 2)	721246
pH 缓冲溶液 4.01 (25 °C) 红, 90 ml 可回溯至 N.I.S.T.	721247
pH-缓冲溶液 7.00 (25 °C) 黄, 90 ml 可回溯至 N.I.S.T.	721248

Tintometer GmbH
 Lovibond® Water Testing
 Schleefstraße 8-12
 44287 Dortmund
 Tel.: +49 (0)231/94510-0
 sales@lovibond.com
 www.lovibond.com
 德国

The Tintometer Limited
 Lovibond House
 Sun Rise Way
 Amesbury, SP4 7GR
 Tel.: +44 (0)1980 664800
 Fax: +44 (0)1980 625412
 sales@lovibond.uk
 www.lovibond.com
 英国

Tintometer China
 9F, SOHO II C.
 No.9 Guanghualu,
 Chaoyang District,
 Beijing, 100020
 Customer Care China Tel.: 4009021628
 Tel.: +86 10 85251111 Ext. 330
 Fax: +86 10 85251001
 chinaoffice@tintometer.com
 www.lovibond.com
 中国

Tintometer South East Asia
 Unit B-3-12, BBT One Boulevard,
 Lebu Nilam 2, Bandar Bukit Tinggi,
 Klang, 41200, Selangor D.E
 Tel.: +60 (0)3 3325 2285/6
 Fax: +60 (0)3 3325 2287
 lovibond.asia@tintometer.com
 www.lovibond.com
 马来西亚

Tintometer Brazil
 Caixa Postal: 271
 CEP: 13201-970
 Jundiaí – SP
 Tel.: +55 (11) 3230-6410
 sales@lovibond.us
 www.lovibond.com.br
 巴西

Tintometer Inc.
 6456 Parkland Drive
 Sarasota, FL 34243
 Tel: 941.756.6410
 Fax: 941.727.9654
 sales@lovibond.us
 www.lovibond.us
 美国

Tintometer India Pvt. Ltd.
 Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
 Sanathnagar Industrial Estate,
 Hyderabad, 500018
 Telangana
 Tel: +91 (0) 40 23883300
 Toll Free: 1 800 599 3891/ 3892
 indiaoffice@lovibond.in
 www.lovibondwater.in
 印度

Tintometer Spain
 Postbox: 24047
 08080 Barcelona
 Tel.: +34 661 606 770
 sales@tintometer.es
 www.lovibond.com
 西班牙