


Lovibond® Colour Measurement Tintometer® Group



TG 268 Gloss Meter



- Handheld Gloss Meter Designed to Give Fast, Precise and Accurate Gloss Readings
- Three Measurement Angles of 20°, 60° and 85°
- Compare Data Quick and Easy With a Data Storage Capacity of Over 5000 Data Sets
- OnGloss Software Included for FREE – Perfect for Detailed Data Analysis

Artigo No: 403045

Handheld and Portable

Weighing only 350 grams, the TG 268 is the perfect lightweight portable gloss meter. Its compact and ergonomic design offers easy one-handed operation, helping to prevent operator fatigue. Offering the possibility of 1,000 measurements with 8 hours battery life enables the TG 268 to be used anywhere on site for a prolonged period of time.

Flexibility

The TG 268 offers the user high flexibility. With detector angles of 20°/ 60°/ 85° the TG 268 can measure low, medium and high gloss levels on a wide range of materials. To enhance flexibility even further, basic, statistical and continuous measurement modes are available to ensure the TG 268 can be set perfectly to the user's needs.

Calibration

Every TG 268 is supplied with a calibration plate and easy to use on screen calibration guide making the whole procedure fast and simple for the user.

FREE Software

As standard, the TG 268 comes with a FREE PC software package. The OnGloss software allows for a detailed data analysis which can then be shared or printed via the optional micro printer accessory.

Suitable for Multiple Standards

The TG 268 is able to support the following standard gloss levels: ASTM D523; ASTM C584; ASTM D2457; BS3900 D5; DIN 67530; DIN EN ISO 2813; EN ISO 7668 and JIS Z 8741.

Aplicação

Plásticos | Produtos Domésticos | Revestimentos | Têxteis

TG 268 Gloss Meter

The TG 268 is a cost-effective handheld gloss meter with a high-end specification. The ergonomic design, flexibility and intuitive touch screen technology makes the TG 268 equal in sophistication to any handheld gloss meter on the market. The meter comes with the ability to select 20°, 60° and 85° measurement angles and the choice of multiple measuring modes making it ideal for quality control in the production process of many industries.

Dados Técnicos

Tipo de Cor	Opaque
Display	TFT 3.5 inch, capacitive touch screen
Interfaces	USB RS 232
Faixa de Medição	0 - 10 unidades de brilho, reprodutibilidade $\pm 0,1$ unidades de brilho, reprodutibilidade $\pm 0,2$ unidades de brilho 10 - 100 unidades de brilho, reprodutibilidade $\pm 0,2$ unidades de brilho, reprodutibilidade $\pm 0,5$ unidades de brilho 100 - 2000 unidades de brilho, reprodutibilidade $\pm 0,2\%$ unidades de brilho, reprodutibilidade $\pm 0,5\%$ unidades de brilho
Measuring Angle	20° / 60° / 85°
Área de Medição	20°: 10 x10 ; 60°: 9 x15 ; 85°: 5 x 36
Faixa de Medição	20°: 0 - 2000 GU ; 60°: 0 - 1000 GU ; 85°: 0 - 160 GU
Division Value	0.1 GU
Armazenamento Interno	Basic Mode: 1000 ; Statistical Mode: 5000 ; Continuous Mode: 5000
Tempo de Medição	1.0 s
Tempo de Vida da Bateria	> 1000 times (within 8 hours)
Portabilidade	Portátil
Idiomas da Interface do Usuário	Inglês
Dimensões	160 x 90 x 75 mm

Texto do Escopo de Entrega

- TG 268 Handheld Gloss Meter
- OnGloss Software (PC)
- Calibration Plate
- USB Cable
- External DC Power Supply
- USB Stick with User Manuals in English, French, German, Spanish, Portuguese and Chinese
- Sturdy Carrying Case

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Alemanha

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
sales@lovibond.uk
www.lovibond.com
Reino Unido

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebuh Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malásia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brasil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
EUA

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
Índia

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Espanha