


Lovibond® Water Testing

Tintometer® Group



PTV6000 Process Turbidimeter with Flow Indicator, Ethernet & Bluetooth®; Laser, EPA

Process Turbidity Simplified



- Online Turbidimeter approved for EPA reporting purposes
- Compatible with AquaLXP mobile app
- On-screen RSD parameter
- Approved by Texas TCEQ as an alternative method for monitoring individual filter effluent from membrane units used for pathogen removal

Part Number: 6154624

Process Simplified - A New Approach

Details Matter. The development of the PTV Series considered every aspect of process turbidity workflow - from installation and setup; daily measurement and control; routine procedures such as calibration, verification and maintenance; to data collection and management.

Smart User Interface - Rethink the Controller

We've replaced the need for a traditional controller with the familiar interface of a smart device. By utilizing a mobile device app, the user experience is enhanced by allowing quick and easy data viewing, calculation of statistics and access to operator instructions and useful tips.

Designed to Save

Save time, money and water by using the PTV system. These instruments are optimized for drinking water applications with unsurpassed low range accuracy (below 1 NTU). It has a variety of features that help users save.

Regulatory Compliant

The PTV Series has instruments that meet EPA and ISO regulatory requirements.

Fluidics Manager

The Fluidics Manager is an additional accessory that streamlines sample flowing into and out of the instrument. This eliminates the need to install and maintain separate devices to control sample entering and exiting the sensor.

Panel Mounting System

A Place for Everything - The Panel Mount is an additional accessory that aids in the installation of key instrument components and accessories.

Two Ways to Interface

Touchscreen Interface - All PTV Series instruments are supplied with an integrated touchscreen. All measurement settings and routine functions such as calibration can be managed directly with the touchscreen without the need for additional devices.

AquaLXP™ Interface - The AquaLXP™ app is an enhanced version of the touchscreen. In addition to being able to perform all of the functions as the touchscreen, users have access to animated instructions of all procedures, advanced data analysis and statistics tools, complete maintenance and repair logs as well as the comfort of using a familiar device.

Wet Standards - for Calibration & Verification

T-CAL Turbidity Standards from Lovibond® Tintometer® are primary standards that are US EPA and ISO compliant.

When you combine our T-CAL Turbidity Standards and our T-CALplus™ packaging, turbidity standards have never been easier to use.

Industry

Municipalities

PTV6000 Process Turbidimeter with Flow Indicator, Ethernet & Bluetooth®; Laser, EPA

The PTV6000 Process Turbidimeter utilizes a laser light source for monitoring filter effluent in a regulatory environment. This model is designed to detect ultra low levels of turbidity, and is ideal for membrane filtration monitoring or plants looking to optimize filter performance.

Technical Data

Optics	Laser
Accuracy	± 2 % of reading from 0 to 10 NTU ± 4 % of reading between 10 to 100 NTU
Display	Touchscreen
Stray Light	smaller 0.005 / 5 mNTU
Displayed Resolution	up to 0.0001 NTU (range dependent) or 5 digits displayed
Repeatability / Precision	better than 1% at 1 NTU
Initial Response	10 % change: 15 seconds @ max flow
Step Response	(T-90), less than 240 seconds at 200 ml/min. at 1 NTU
Signal Averaging	User Selectable: 1, 3, 6, 10, 30, 60, and 90 seconds, defaulted to 30 seconds
Sample Temperature	0 - 50 °C (32 to 122 °F) max sample temperature: 70 °C (158 °F)
Sample Flow	30 to 500 ml/min, optimal flow: 50 to 80 ml/min
Sample Inlet Connection	1/4-inch NPT female, 1/4-inch compression fitting tubing (included)
Sample Outlet (Drain) Connection	3/8-inch NPT female, 3/8-inch hose barb tubing (included)
Power Requirements	90 to 264 VAC, 50/60 Hz. Auto Select
Sample Inlet Tubing	1/4-inch OD or 6 mm OD
Sample Outlet Tubing	3/8-inch OD or 9 mm OD
Turbidimeter Body Drain	Quick connect with integrated check valve
Calibration	One Point Calibration at 5.0 or 20 NTU with any regulatory approved formazin
Analog Output: Measurement Module	1 selectable 0 - 20 mA or 4 - 20 mA; output span programmable over any portion of the measurement range
Analog Output: Junction Box	1 selectable 0 - 20 mA or 4 - 20 mA; output span programmable over any portion of the measurement range
Alarms	Three set-point alarms, each equipped with an SPDT relay with unpowered contacts rated 5 A resistive load at 230 V, AC
Digital protocol	Modbus TCP (Ethernet)
Enclosure Type: Junction Box	Fiber reinforced polyester
Enclosure Rating: Junction Box	IP 66
Safety	Listed by TÜV Rheinland to UL 61010A-1: Certified by TÜV Rheinland to CSAC22.2 No. 1010.1: CE Certified by TÜV Rheinland to EN 61010-1
Immunity	CE certified by TÜV Rheinland to EN 61326 (Industrial Levels)
Mounting Hardware	Turbidimeter Sensor - Slotted Mounting Bracket that can be affixed to any vertical surface or panel (Optional). Junction Box - Direct mounting to any vertical surface or panel (Optional)
Method of Verification	Wet Standards or dry verification device
Limit of Determination	0.0001 NTU
Limit of Detection	0.001 NTU
Flow Indicator	yes

Portability	Process
Environmental Conditions	5 - 50 °C (41 to 122 °F), rel. humidity 5 - 95 % (Non-condensing)
Stock Conditions	-40 - 60 °C (-40 - 140 °F)
Compliance	EPA
Dimensions	158.5 x 340.4 x 334.5 mm

Title	Part Number
Kit, Bubble Trap Cover and O-ring, for PTV 6000	19806-048
Assembly, Float	19806-054
Assembly, Fluidics Manifold	19806-056
Constant Head Height Regulator	19806-058
Kit, Fittings & Tubing	19806-059
T-CALplus Calibration Tube Assembly (Blue Tube)-	19806-062
Cleaning Tube Assembly (Black Tube)	19806-072
Kit, Bubble trap cover Replacement (comes with O-ring)	19806-077
Kit, Knob for bubble trap	19806-079
Kit, Drain fitting	19806-080
Kit, Drain cover	19806-081
Kit, Flow body assembly, with Flow Meter	19806-083
Kit, Flow body assembly, without Flow Meter	19806-084
Kit, Illuminator Lens Sub Assembly	19806-085
Kit, Installation Connectors	19806-086
Rotometer, 25 to 100 mL/min	19806-087
Panel, Instrument and Sample Management	19806-088
Brass mounting cup assembly	19806-106
Dry Verification STD, High Range (> 10 NTU)	19806-110
Dry Verification STD, Low Range (< 10 NTU)	19806-111
Mounting Cleat with Interlock, for PTV 6000	19806-119
Fuse, 1.6A, 250VAC	19806-206
Illuminator O-ring	19806-407
O-ring, for Beam Dump	19806-416
Tubing, 1/4" OD, black, Polyethylene	19806-429
O-ring, Rear Drain cover	19806-434
Fitting, Quick Connect, Male	19806-436
Lanyard Strap	19806-448
Fitting, Quick Connect, Female	19806-449
Plug for Conduit holes	19806-487
Valve; 1/4" Tubing Quick Connect	19806-494
Tablet Wall Mount	19806-521
Strain Relief, 3/8" NPT	19806-527
Tubing, 3/8" ID x 1/2" OD x 1/16" Wall, Clear PVC	19806-531
Seal, Bubble trap cover, -241 -	19806-554
Insert, Measurement Module Holder, Instrument Panel	19806-570
Measurement Module, PTV 6000	19806-706
Measurement Module, PTV 6000 with, with Bluetooth®	19806-707
Kit, Beam Dump Guard / Interlock, Fitting & O-rings, for PTV 6000	19806-716
Pad, Application, Microfiber, w/pocket	19806-803
Rinse bottle, 500 ml	420056
T-CALplus® -Standard, 0.30 NTU, Standard for Verification	48010035
T-CALplus® -Standard, 1.00 NTU, Standard for Verification	48010135
T-CALplus® -Standard, 5.00 NTU, Standard for Calibration	48010235
T-CALplus® -Standard, 20 NTU, Standard for Calibration	48010335
T-CAL®-Standard, 0,30 NTU, 500 ml	48011050
T-CAL®-Standard, 1,00 NTU, 500 ml	48011150
T-CAL®-Standard, 5,00 NTU, 500 ml	48012250

Title	Part Number
T-CAL®-Standard, 20,00 NTU, 500 ml	48012350
Cleaning Solution	54010435
Detergent Solution	54011010
Scale Remover	54013003

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Germany

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
sales@lovibond.uk
www.lovibond.com
UK

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebuh Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaysia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brazil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
USA

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
India

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Spain